

**TOP GLOVE**

**TOP QUALITY, TOP EFFICIENCY**

More Than Just Gloves

# VINYL GLOVE

Powdered & Powder Free



An economical solution for individuals who are allergic to Natural Rubber Latex



## APPLICATION



Food Handling



Hotel and Catering



Beauty and Salon



Cleaning and Housekeeping



Painting



General Use

An economical solution for individuals who are allergic to Natural Rubber Latex

Free from latex protein, eliminating Type I Immediate Hypersensitivity reaction

Ambidextrous with wearing convenient, **soft and comfortable**



Odour free, results from special formulation



Ease in donning due to the excellent smooth inner surface



In grip slightly tacky surface

# VINYL GLOVE

## Powdered & Powder Free



### Quality Standard

- Manufactured under ISO 9001:2015 Quality Management System
- Manufactured under ISO 13485:2016 Quality Management System

### Glove Sizes

- Small, Medium, Large, Extra-Large

### Product Specifications

- Type** : Powdered & Powder-Free, Non-sterile
- Material** : Polyvinyl Chloride Paste Resin
- Colour** : Clear, Blue, Black, Pink, Light Purple
- Design &**
- Features** : Ambidextrous, smooth surface, beaded cuff
- Storage** : The gloves shall maintain their properties when stored in cool and dry condition  
Avoid direct sunlight
- Shelf-life** : 5 years from the date of manufacture with the above storage condition

### Physical Dimensions

Dimensions	Standards		
	Top Glove	ASTM D5250	EN 455
<b>Length (mm)</b>	Min 230 or Min 240	Min. 230	Min 240
<b>Palm Width (mm)</b>			
• S	85 +/- 5	85 +/- 5	80 +/- 10
• M	95 +/- 5	95 +/- 5	95 +/- 10
• L	105 +/- 5	105 +/- 5	110 +/- 10
• XL	115 +/- 5	115 +/- 5	≥ 110
<b>Thickness : Single Wall (mm)</b>			
• Finger	Min 0.04	Min 0.08	N/A
• Palm	Min 0.04	Min 0.08	N/A

### Physical Properties

Description	Standards		
	Top Glove	ASTM D5250	EN 456
<b>Tensile Strength (MPa)</b>			
• Before Aging	Min 11	Min 11	N/A
• After Aging	Min 11	Min 11	
<b>Elongation at Break (%)</b>			
• Before Aging	Min 300	Min 300	N/A
• After Aging	Min 300	Min 300	
<b>Median Force at Break (N)</b>			
• Before Aging	Min 3.6	N/A	Min 3.6
• After Aging	Min 3.6		Min 3.6

If you have any enquiries on our products, please contact :

### TOP GLOVE SALES & CORPORATE OFFICE

Top Glove Tower, 16, Persiaran Setia Dagang, Setia Alam, Seksyen U13, 40170 Shah Alam, Selangor D.E., Malaysia.

+603 3362 3098

+603 3362 5096 (Sales)

SCAN FOR  
VINYL DISPOSABLE  
GLOVE



SCAN TO PROVIDE  
FEEDBACK AND  
VISIT OUR WEBSITE



sales@topglove.com.my

https://www.facebook.com/topglovecorp

www.topglove.com